







## CHARACTERISTIC FEATURES TECHNICAL DATA SENSORS EQUIPMENT APPEARANCE

Sensonic tried and tested hand-held analyser. Its small dimensions and light weight makes it very convenient for technicians that use analyser on a daily basis.

Sensonic 1400 can be equipped with up to 4 electrochemical cells. By default fitted with Li-ion battery.

Suitable for a soot test using electronically controlled gas volume.

It holds big memory capable of storing 32 measurement reports.

Manufactured according to the principles of EN50379.

An attractive alternative to other, bigger analysers.

## CHARACTERISTIC FEATURES TECHNICAL DATA SENSORS EQUIPMENT APPEARANCE

- Equipped with 3 or 4 electrochemical cells (typical configuration: O<sub>2</sub>, CO, NO/NO<sub>x</sub>, SO<sub>2</sub>)
- · Works with an external portable printer via wireless communication (IR LED)
- Built-in rechargeable Li-ion battery for up to 10 hours of operation
- Probe holder with a standard M30x1 fitting, fits all madur gas probes with the K-type or S-type thermocouples
- · Availability of soot measurements (with proper probe holder)
- · Built-in pressure sensor for chimney draft measurements and continuous pump flow control
- Optional differential pressure sensor for measurements of chimney draft and flow velocity (with help of Pitot tube)
- NOTE that two versions of analyser are available: standard version with single pressure sensor version with additional differential pressure sensor (that allows to perform measurements of gas flow velocity)
- · Cooperation with digital RH and temperature probe
- Measurements of gas and ambient temperatures
- Results presented on LCD display (128 \* 64) with back-lighting
- Built-in large memory for results
- · Firmware for gas calibrations
- · Calculations of many additional parameters



2

CHARACTERISTIC	FEATURES	TECHNICAL DATA	SENSORS	EQUIPMENT	APPEARANCE		
SENSONIC 1400 GA	AS ANALYSER	VERSION A		VERSION B			
Dimensions (W * H * D)		SINGLE PRESSURE	SINGLE PRESSURE SENSOR SECOND DIFFERENTIAL PRESSURE SENSOR 243 mm * 130 mm * 60 mm				
Dimensions with gas co	nnectors (W * H	* D) 257 mm * 130 r	257 mm * 130 mm * 60 mm 271 mm * 130 mm * 60 n		* 60 mm		
Weight (4-sensors) with	nout accessories	615 g		635 g			
Casing material		ABS cas	ABS case, rubber protective boot (optional)				
Operating conditions		T: 10°C ÷	T: 10°C ÷ 50°C RH: 5% ÷ 90% (non-condensing)				
Storing temperature			-20°C ÷ +	55°C			
Power supply		Built-in Li	Built-in Li-ion rechargeable battery (1600 mAh)				
Operating time (fully charged battery)			Up to 16h				
Number of gas sensors			3 0r 4				
Data memory			64 measurement reports				
Display		with va	Graphical LCD 128 * 64 with variable contrast and LED backlighting				
Printer		External th	External thermal IR printer MCP 8850 with charger				
Gas pump		C	Diaphragm, max 0,6 ÷ 0,9 l/min				
Communication interfac	ce with PC compu	iter	RS-232C				
Gas filtering		In-line	filter included in	the gas probe hose			

### MEASUREMENTS

Variable	Method	Range   Resolution	Accuracy	Time (T <sub>90</sub> )
T <sub>gas</sub> - gas temperature	K-type thermocouple	-10 ÷ 1000°C   0,1°C	± 2°C	10 sec
T <sub>gas</sub> - gas temperature	S-type thermocouple	-10 ÷ 1000°C   0,1°C	± 2°C	10 sec
T <sub>amb</sub> - boiler intake air temperature	PT500 resistive sensor	-10 ÷ 100°C   0,1°C	± 2°C	10 sec
Differential pressure	Silicon piezoresistive pressure sensor	-25 hPa ÷ +25 hPa   1 Pa (0,01hPa)	± 2Pa abs. or 5% rel.	10 sec
Gas flow velocity (optional)	Indirect, with Pitot tube & second pressure sensor		0,3 m/s abs. or 5% rel.	10 sec
Lambda λ- excess air number	Calculated	1 ÷ 10   0,01	± 5% rel.	10 sec
qA - stack loss	Calculated	0÷100%   0,1%	± 5% rel.	10 sec
Eta η - combustion efficiency	Calculated	0÷120%   0,1%	± 5% rel.	10 sec
RH- relative humidity (special probe needed)	SHT11 capacitive polymer sensor	5÷95%  1%	± 5% abs.	30 sec



CHARACTERISTIC FEATURE	S TECHNICAL D	ATA SENSORS E	QUIPMEN	T APPEARANCE
Method	Range   Resolution	Accuracy	Time (T <sub>90</sub> )	Conformity
O <sub>2</sub> - OXYGEN				
Electrochemical	20,95%   0,01%	± 0,2% abs. or 5% rel.	45 sec	EN 50379; CTM-030
Electrochemical	25,00%   0,01%	± 0,2% abs. or 5% rel.	45 sec	EN 50379; CTM-030
CO - CARBON MONOXIDE				
Electrochemical	2 000 ppm   0,1 ppm	± 5 ppm abs. or 5% rel.	45 sec	EN 50379; CTM-030
Electrochemical	4 000 ppm   1 ppm	± 5 ppm abs. or 5% rel.	45 sec	EN 50379; CTM-030
Electrochemical	20 000 ppm   1 ppm	± 10 ppm abs. or 5% rel.	45 sec	EN 50379; CTM-030
Electrochemical	10%  0,001 %	± 0,005% abs. or 5% rel.	45 sec	EN 50379; CTM-030
Electrochem., with H2 compensation	4 000 ppm   1 ppm	± 5 ppm abs.or 5% rel.	45 sec	EN 50379; CTM-030
NO - NITRIC OXIDE				
Electrochemical	2 000 ppm   0,1 ppm	± 5 ppm abs. or 5% rel.	70 sec	EN 50379; CTM-030
NO <sub>2</sub> - NITROGEN DIOXIDE				
Electrochemical	1 000 ppm   0,1 ppm	± 5 ppm abs. or 5% rel.	45 sec	EN 50379; CTM-030
SO <sub>2</sub> - SULPHUR DIOXIDE				
Electrochemical	2 000 ppm   0,1 ppm	± 5 ppm abs. or 5% rel.	45 sec	EN 50379
H <sub>2</sub> S- HYDROGEN SULPHIDE				
Electrochemical	2 000 ppm   0,1 ppm	± 5 ppm abs. or 5% rel.	45 sec	

### CHARACTERISTIC FEATURES TECHNICAL DATA SENSORS

EQUIPMENT APPEARANCE

### STANDARD EQUIPMENT

SUPPLIED ALONG WITH THE DEVICE

- Carrying case for analyser and accessories
- · Power supply (charger) for the built-in Li-ion battery with selected type of mains plug
- · Comparison scale with paper filters for the soot test
- · Software CD with programs and manuals
- 2,5m RS-232C communication cable with DB9 female connector

#### ADDITIONAL EQUIPMENT

NECESSARY FOR THE ANALYSER TO WORK

Probe holder

Together with an exchangeable gas probe pipe the holder is a complete gas probe for extraction of gas samples. It has a single gas tube ended with quick coupler and electric cable ended with a 4-pin connector. Gas probe pipe is mounted with a M30x1 fastening. Probe holder is equipped with an in-line filter with a condensation trap (pore size of the filter inlet is  $5\mu$ m). Probe holder is available in two versions:

- heated (with a slit for a filter for soot measurement test),

- unheated (without a possibility to perform soot test).

#### · Gas probe pipe

Gas probe is immersed in the gas duct and is supposed to extract the gas sample and to measure its temperature.

Exchangeable probes are easily connected to probe holders (with M30x1 fastening). They have thermocouple type K (in some configurations type S) for measurement of gas temperature and a threaded fixing cone. With the probe holder is a complete gas probe. There are many probe pipes available. They differ in length and working temperature. For work efficiency it is advised to own different probe pipes to be able to adjust to the measurement place.

### **OPTIONAL EQUIPMENT & SPARE PARTS**

Portable printer & printer paper

Portable printer (battery operated), communicates with the analyser via wireless HP-IR interface. Allows to print measurement results instantly on the 58mm thermal paper. The printer is delivered together with 4 Ni-MH rechargeable batteries and a single roll of paper. The mains adapter for the charger can be ordered appropriately in the AU/EU/UK/US version.

ordering codes: printer - M20-2DHP2 battery charger with EU plug - M20-2DHP1 battery charger with US plug - M20-2DHP3 battery charger with UK plug - M20-2DHP4 58mm thermal paper roll - V-THP5701

RH and ambient temperature probe
Probe for RH and ambient temperature measurements.
Not-suitable for inside stack measurements (working temperature up to 120°C).

ordering code: Z14-SON-HUM

Z12-SENS-TEMP

#### Ambient temperature sensor

This ambient temperature sensor on a 3m cable is used for measurement of the boiler's inlet air. ordering code:











#### SENSORS **CHARACTERISTIC FEATURES TECHNICAL DATA**

#### · Anchor cone for PT500 ambient temperature sensor

This cone allows fitting the temperature sensor into holes with different diameter.

Magnetic holder for PT500 sensor

This magnetic holder allows to safely hang the sensor on a metal surface. ordering code:

Pitot tube

Pitot tube is an accessory that allows to perform measurement of the flow velocity of the gas stream. The measurement is performed indirectly - Pitot tube is connected to analyser's differential pressure sensor. Analyser recalculates the differential pressure on the Pitot tube's outlets to velocity.

A few lengths of tubes are available. Pitot tube has 2m gas tubings to connect it with the analyser.

ordering codes: pitot tube 800mm - Z00-PITOT-8002 pitot tube 500mm - Z00-PITOT-5002

 RS232C to USB converter 2.5m cable that allows to connect the analyser (its RS232C port) with USB port in PC

computer (especially valuable when PC is not equipped with COM port). ordering code: Z12-USB-ADAP

 Bluetooth communication module Module connected to the analyser's RS232C port, allows to communicate with PC computer over Bluetooth protocol.

ordering code: Z12-BLUE-TOOTH

ordering code: Z14-CONE-PT500

Z14-MAGN-PT500

Leatherette casing

· Li-ion rechargeable battery

Soft casing (for the analyser alone) made from leatherette, protects the anayser during transport.

ordering code: Z14-ETUI1

Rubber protector

Pressure kit

Special rubber protector for the analyser's casing. Protects the analyser against hits and blows. Shoulder strap eases carrying the analyser.

> ordering code: Z14-RUBBER-001

Pressure kit allows to perform leakage test of the pneumatic / gas installations.

ordering code: Z02-LEAK-TEST-KIT

ordering code: Z14-BAT-CHARGER 02

**Z14-FILTER-INLINE** 

 In-line filter In-line filter for Sensonic 1400 and Sensonic 1400 probe holders. ordering code:

 In-line filter insert 12mm/5µm and 12mm/20µm Filter insert for all the types of in-line filters.

Requires differential pressure sensor to operate.

Rechargeable Li-ion battery, 3,6V, 1600mAh (or better).

ordering codes: 5µm insert - V-FELM082 20µm insert -V-FELM252



EQUIPMENT

**APPEARANCE** 




















### sensonic-analysers.com sales@sensonic-analysers.com



### Sensonic 1400 - brochure v01.02 en






sensonic-analysers.com sales@sensonic-analysers.com

7


CHARACTERISTIC FEATURES TECHNICAL DATA SENSORS EQUIPMENT APPEARANCE

### EXAMPLE PRINTSCREEN

Esc



1 1/3	Triple	
19.53	20.48	7.0 <sub>2</sub>
0.89	0.30	%C02
1	0	PPmCO
		PPM <sup>ND</sup> ×
Esc	1-2-3	++



### EXAMPLE SCREENSHOT FROM THE PC PROGRAM

++

OK

Analyzer printo	uts defining		×
User defined strings	Printout preview		
0		Line: 1 Code: 42	
	PrintOut 1 PrintOut 2 PrintOut 3 PrintOut 4		
1	<b>_</b>	Results	
2		C	-
	1#1	-	_
3	Sensonic 1400	Special lines	
4	Sensonic 1400	Report: 1-2-3 #0000	-
5		User defined strings	
	1 Report: 1-2-3 #0000	C	
6	01-01-01 12:57		•
7	Light oil 1	Separating lines	
8	Averaging time: 2 min	0	-
• <u> </u>	5 Client nr: 00001		
9	Operator:	C No line Send to	
10		analyzer analyzer	
	02 5.12 %	C Empty line	1
11	C02 10.04 %	Remove line Open file	8
12	10 C0 163.2 ppm		
	NO 163.2 ppm	Insert line Save	
13	NOx 78.8 ppm		
14	NOX 70.0 ppm	Defeat	
45	10X	Print partial results Default	
15			
Operator	15 CO in mg 204 mg/Nm3  _	Fast printer Close	